

DXE 5 Series Wafer Expander

DXE 5 Series Wafer Expander

The DXE 5 Series wafer expander is used for expanding wafers after the singulation/dicing process. This prevents die-edge chipping during shipping or the pick and place operation.

Functionality:

- The DXE 5 Series has been designed to expand the space between diced semiconductor die by omni-directional stretching of the plastic film on which these die have been mounted. The stretching is done over concentric hoop sets that retain the stretched plastic films.
- The DXE heats the tape to improve the tape flexibility during the expansion process. It has been preset at the factory for 150 +/- 5° F (66 +/- 2.5° C). Operation at 150° F (66° C) is recommended for most films. The temperature is adjustable to accommodate a wide range of tapes and films.



DXE 5 Series Expander Applications:

- Laser diodes
- Wafer mounting


- LEDs
- Transfer of wafers from film frames to hoops



dynatex[™]
I N T E R N A T I O N A L

Mounting wafer tape to the hoops:


The inner hoop is placed on the heated chuck with the rounded edge facing up. The wafer mount tape is positioned over the heated chuck and the inner hoop. The outer hoop is placed inside the lid with the rounded edge facing down.



The lid is pneumatically actuated, forcing the outer hoop over the inner hoop. The tape is mounted with the adhesive side up and smooth side down. The outer hoop comes in contact with the adhesive surface. The outer hoop grips the tape and pulls it down over the inner hoop. The tape slides over the inner hoop thereby becoming stretched.

Expanding a wafer:

The hoop set with the wafer mount tape and a diced wafer is placed onto the heated chuck. An additional outer hoop is placed inside the lid.




The lid is actuated, forcing the outer hoop over the inner hoop and pushing the first outer hoop down and off the inner hoop. This action pulls the tape down over the inner hoop, stretching the tape and thereby expanding the wafer. This step can be repeated to expand the wafer by the desired amount.

Transferring from film frames to hoops:

To transfer a wafer from film frame to hoops or grip rings simply load the outer hoop in the lid and the inner hoop on the heated chuck, insert the wafer and film frame then actuate by depressing both start buttons, as a safety feature.

DXE 5 Series Wafer Expander Specifications

Power Required	100/120 VAC 3 amp OR 220/240 VAC 1.5 amp, 50/60Hz
Operating Temperature	150 +/- 5° F (66+/- 2.5° C)
Height	8 in (200 mm)
Width	8.5 in (216 mm)
Depth	12.5 in (315 mm)



Although the information and recommendations set forth herein are presented in good faith and believed to be correct, Dynamatex International makes no representations as to their completeness or accuracy. Information is supplied upon the condition that the persons receiving will make their own verification and determination as to its suitability for their purposes prior to use. In no event will Dynamatex International be responsible for damages of any nature whatsoever resulting from the use of or reliance upon this information. NO REPRESENTATION OR WARRANTIES, EITHER EXPRESSED OR IMPLIED, OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER NATURE ARE MADE HEREUNDER WITH RESPECT TO INFORMATION OR PRODUCT TO WHICH INFORMATION REFERS.